




FOCAL LENGTH (EFL): 38 ±0,38

BACK FOCAL LENGTH (BFL): 33,03

- 1 AR COATING: VIS-NIR
R(ABS) ≤ 0,25% AT 880nm @ 0° AOI
R(AVG) ≤ 1,25% FROM 400-870nm @ 0° AOI
R(AVG) ≤ 1,25% FROM 890-1000nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	17,421±0,017 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	24		Øe	24
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
SCALE: NONE
λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

25mm Dia, x 38mm FL VIS-NIR Coated, UV Plano-Convex Lens

DWG NO

63806

SHEET SIZE
A4

SHEET
1 OF 1