




FOCAL LENGTH (EFL): $4 \pm 0,04$
 BACK FOCAL LENGTH (BFL): $3,57$

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$3,4 \pm 0,003$ CX	GLASS N-LaSF9 850/322	R	∞ PL
Øe	1,5		Øe	1,5
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	52,94'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6$ nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

2,0mm Dia, x 4,0mm FL, Uncoated,
Plano-Convex Lens

DWG NO

65256

SHEET SIZE
A4

SHEET
1 OF 1