





FOCAL LENGTH (EFL): 45 ±0,45
BACK FOCAL LENGTH (BFL): 43,98

1 AR COATING: 532nm V-COAT
R(ABS) < 0,25% @ 532nm @ 0° AOI

LEFT SURFACE			MATERIAL		RIGHT SURFACE			
R	23,26±0,023 CX		GLASS	N-BK7 517/642	R	∞ PL		
Øe	8,1				Øe	8,1		
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm		
4/	-				4/	1,93'		
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)		
6/	-				6/	-		
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE				
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				9,0mm Diameter x 45,0mm FL, 532nm V-Coat, PCX Lens				
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	65478	SHEET SIZE A4	SHEET 1 OF 1