





FOCAL LENGTH (EFL): 38 ±0,38
 BACK FOCAL LENGTH (BFL): 33,03

1 AR COATING: NONE

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R	17,421±0,017 CX		GLASS FUSED SILICA 458/678	R	∞ PL	
Øe	24			Øe	24	
3/	2 (0,2) λ=632,8 nm			3/	2 (0,2) λ=632,8 nm	
4/	-			4/	2,18'	
5/	20 - 10 (MIL-PRF-13830B)			5/	20 - 10 (MIL-PRF-13830B)	
6/	-			6/	-	
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				25mm Diameter x 38mm FL, 355nm Coated, Laser Grade PCX Lens		
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	67953
			SHEET SIZE			SHEET
			A4			1 OF 1