




FOCAL LENGTH (EFL): 75 ±0,75  
BACK FOCAL LENGTH (BFL): 71,96

1 AR COATING: NONE

| LEFT SURFACE |                          | MATERIAL                   | RIGHT SURFACE |                          |
|--------------|--------------------------|----------------------------|---------------|--------------------------|
| R            | 34,385±0,034 CX          | GLASS FUSED SILICA 458/678 | R             | ∞ PL                     |
| Øe           | 24                       |                            | Øe            | 24                       |
| 3/           | 2 (0,2) λ=632,8 nm       |                            | 3/            | 2 (0,2) λ=632,8 nm       |
| 4/           | -                        |                            | 4/            | 2,18'                    |
| 5/           | 20 - 10 (MIL-PRF-13830B) |                            | 5/            | 20 - 10 (MIL-PRF-13830B) |
| 6/           | -                        |                            | 6/            | -                        |

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 25mm Diameter x 75mm FL, 355nm Coated, Laser Grade PCX Lens

DWG NO 67955

SHEET SIZE A4 SHEET 1 OF 1