




FOCAL LENGTH (EFL): 25 ±0,25  
 BACK FOCAL LENGTH (BFL): 22,31

1 AR COATING: NONE

| LEFT SURFACE |                          | MATERIAL                   | RIGHT SURFACE |                          |
|--------------|--------------------------|----------------------------|---------------|--------------------------|
| R            | 11,462±0,011 CX          | GLASS FUSED SILICA 458/678 | R             | ∞ PL                     |
| Øe           | 11                       |                            | Øe            | 11                       |
| 3/           | 2 (0,2) λ=632,8 nm       |                            | 3/            | 2 (0,2) λ=632,8 nm       |
| 4/           | -                        |                            | 4/            | 2,18'                    |
| 5/           | 20 - 10 (MIL-PRF-13830B) |                            | 5/            | 20 - 10 (MIL-PRF-13830B) |
| 6/           | -                        |                            | 6/            | -                        |

|                                                                                       |                |             |                                                                                                                  |  |                                                                                                    |  |  |              |
|---------------------------------------------------------------------------------------|----------------|-------------|------------------------------------------------------------------------------------------------------------------|--|----------------------------------------------------------------------------------------------------|--|--|--------------|
| PROTECTIVE CHAMFERS AS NEEDED                                                         |                |             | FIRST ANGLE<br>PROJECTION<br> |  |  Edmund Optics® |  |  |              |
| ROHS:<br>COMPLIANT                                                                    | SCALE:<br>NONE | λ = 587,6nm |                                                                                                                  |  | TITLE<br>12mm Diameter x 25mm FL, 355nm<br>Coated, Laser Grade PCX Lens                            |  |  |              |
| SPECIFICATIONS SUBJECT TO CHANGE WITHOUT<br>NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY |                |             | ALL DIMS<br>IN: mm                                                                                               |  |                                                                                                    |  |  | DWG NO 67950 |
| FOR INFORMATION ONLY: DO NOT MANUFACTURE<br>PARTS TO THIS DRAWING                     |                |             |                                                                                                                  |  | SHEET SIZE A4                                                                                      |  |  |              |
| INDICATIONS IN ACCORDANCE WITH ISO 10110                                              |                |             | SHEET 1 OF 1                                                                                                     |  |                                                                                                    |  |  |              |