




FOCAL LENGTH (EFL): 35 ±0,35

BACK FOCAL LENGTH (BFL): 30,42

1 AR COATING: 405nm V-COAT
R(ABS) < 0,25% @ 405nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	18,11±0,018 CX	GLASS N-BK7 517/642	R	∞ PL
Øe	24		Øe	24
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 587,6nm

FIRST ANGLE
PROJECTION



EO® Edmund Optics®

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm

TITLE

25,0mm Diameter x 35,0mm FL, 405nm
V-Coat, PCX Lens

DWG NO

69346

SHEET SIZE
A4

SHEET
1 OF 1