




FOCAL LENGTH (EFL): 20 ± 0,2

BACK FOCAL LENGTH (BFL): 17,69

1 AR COATING: 980nm V-COAT
R(ABS) < 0,25% @ 980nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	10,335±0,01 CX	GLASS N-BK7 517/642	R	∞ PL
Øe	11		Øe	11
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 587,6nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

12,0mm Diameter x 20,0mm FL, 980nm
V-Coat, PCX Lens

DWG NO

69552

SHEET SIZE
A4

SHEET
1 OF 1