


| LEFT SURFACE |                          |  | MATERIAL                 |  | RIGHT SURFACE |                          |
|--------------|--------------------------|--|--------------------------|--|---------------|--------------------------|
| R            | 258,4±0,258 CX           |  | GLASS    N-BK7   517/642 |  | R             | ∞ PL                     |
| Øe           | 49                       |  |                          |  | Øe            | 49                       |
| 3/           | 3 (0,5) λ=632,8 nm       |  |                          |  | 3/            | 3 (0,5) λ=632,8 nm       |
| 4/           | -                        |  |                          |  | 4/            | 1,93'                    |
| 5/           | 40 - 20 (MIL-PRF-13830B) |  |                          |  | 5/            | 40 - 20 (MIL-PRF-13830B) |
| 6/           | -                        |  |                          |  | 6/            | -                        |

|                                                                                    |                |             |                                                                                     |                                                                                                    |                                                      |        |       |                  |
|------------------------------------------------------------------------------------|----------------|-------------|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|------------------------------------------------------|--------|-------|------------------|
| PROTECTIVE CHAMFERS AS NEEDED                                                      |                |             | FIRST ANGLE<br>PROJECTION                                                           |  Edmund Optics® |                                                      |        |       |                  |
| ROHS:<br>COMPLIANT                                                                 | SCALE:<br>NONE | λ = 587,6nm |                                                                                     |                                                                                                    |                                                      |        |       |                  |
| SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY |                |             |  | TITLE                                                                                              | 50,0mm Diameter x 500,0mm FL, 980nm V-Coat, PCX Lens |        |       |                  |
| FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING                     |                |             |                                                                                     | ALL DIMS<br>IN:                                                                                    | mm                                                   | DWG NO | 69586 | SHEET SIZE<br>A4 |
| INDICATIONS IN ACCORDANCE WITH ISO 10110                                           |                |             |                                                                                     |                                                                                                    |                                                      |        |       |                  |