





FOCAL LENGTH (EFL): 42 ±0,42
 BACK FOCAL LENGTH (BFL): 40,22

1 AR COATING: 980nm V-COAT
 R(ABS) < 0,25% @ 980nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R	21,71±0,022 CX		GLASS N-BK7 517/642	R	∞ PL	
Øe	11			Øe	11	
3/	3 (0,5) λ=632,8 nm			3/	3 (0,5) λ=632,8 nm	
4/	-			4/	1,93'	
5/	40 - 20 (MIL-PRF-13830B)			5/	40 - 20 (MIL-PRF-13830B)	
6/	-			6/	-	
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	12,0mm Diameter x 42,0mm FL, 980nm V-Coat, PCX Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				DWG NO	69555	SHEET SIZE A4
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm		