




NOTES:

- 1. SUBSTRATE: POLYMER FILM XP40HT-18
- 2. TEMPERTURE RESISTANCE (°C x HOURS):
 - HEAT: 100 x 1,000
 - COLD: -40 x 1,000
 - HUMIDITY: 80 x 90% RH x 1,000
- 3. WAVELENGTH RANGE: 400 -700 nm
- 4. POLARIZATION EFFICIENCY (%): >99.5
- 5. TRANSMISSION (%):
 - SINGLE: 40
 - PARALLEL: 32.2
 - CROSSED: <0.005
- 6. EXTINCTION RATIO: 5000:1
- 7. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]			
THIRD ANGLE PROJECTION 		TITLE	500 x 600mm HIGH-TEMPERTURE LINEAR POLARIZING FILM (XP40HT-18)
ALL DIMS IN	mm	DWG NO	13916
			SHEET 1 OF 1