





**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**






SPECIFICATION	VALUE
CUT-OFF WAVELENGTH	400nm $\pm$ 2%
TRANSMISSION BAND	250 - 385nm
REJECTION BAND	420 - 485nm
PASSBAND TRANSMISSION	>85%
REJECTION BAND BLOCKING	$\geq$ 2.0
CLEAR APERTURE	80%
SURFACE QUALITY	40-20
TRANSMITTED WAVEFRONT	$\lambda/4$ P-V
SLOPE FACTOR	$\pm$ 3%
ANGLE OF INCIDENCE (DEG)	0°
COATING TYPE	Traditional Coated
SUBSTRATE	UV Grade Fused Silica

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY


EFL (AT 587.6nm)	NA	 <b>Edmund Optics®</b>		
BFL (AT 587.6nm)	NA	TITLE	400nm 25mm Diameter, OD 2 Shortpass Filter	
ALL DIMS IN	mm	DWG NO	47285	SHEET 1 OF 1

**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**






SPECIFICATION	VALUE
CUT-OFF WAVELENGTH	450nm $\pm$ 2%
TRANSMISSION BAND	250 - 430nm
REJECTION BAND	470 - 545nm
PASSBAND TRANSMISSION	>85%
REJECTION BAND BLOCKING	$\geq$ 2.0
CLEAR APERTURE	80%
SURFACE QUALITY	40-20
TRANSMITTED WAVEFRONT	$\lambda/4$ P-V
SLOPE FACTOR	$\pm$ 3%
ANGLE OF INCIDENCE (DEG)	0°
COATING TYPE	Traditional Coated
SUBSTRATE	UV Grade Fused Silica

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY


EFL (AT 587.6nm)	NA	 <b>Edmund Optics®</b>		
BFL (AT 587.6nm)	NA	TITLE	450nm 25mm Diameter, OD 2 Shortpass Filter	
ALL DIMS IN	mm	DWG NO	47286	SHEET 1 OF 1

**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**






SPECIFICATION	VALUE
CUT-OFF WAVELENGTH	500nm $\pm$ 2%
TRANSMISSION BAND	250 - 480nm
REJECTION BAND	520 - 610nm
PASSBAND TRANSMISSION	>85%
REJECTION BAND BLOCKING	$\geq$ 2.0
CLEAR APERTURE	80%
SURFACE QUALITY	40-20
TRANSMITTED WAVEFRONT	$\lambda/4$ P-V
SLOPE FACTOR	$\pm$ 3%
ANGLE OF INCIDENCE (DEG)	0°
COATING TYPE	Traditional Coated
SUBSTRATE	UV Grade Fused Silica

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY


EFL (AT 587.6nm)	NA	 <b>Edmund Optics®</b>		
BFL (AT 587.6nm)	NA	TITLE	500nm 25mm Diameter, OD 2 Shortpass Filter	
ALL DIMS IN	mm	DWG NO	47287	SHEET 1 OF 1

**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**






SPECIFICATION	VALUE
CUT-OFF WAVELENGTH	550nm±2%
TRANSMISSION BAND	400 - 530nm
REJECTION BAND	575 - 725nm
PASSBAND TRANSMISSION	>85%
REJECTION BAND BLOCKING	≥2.0
CLEAR APERTURE	80%
SURFACE QUALITY	40-20
TRANSMITTED WAVEFRONT	$\lambda/4$ P-V
SLOPE FACTOR	±3%
ANGLE OF INCIDENCE (DEG)	0°
COATING TYPE	Traditional Coated
SUBSTRATE	UV Grade Fused Silica

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY


EFL (AT 587.6nm)	NA	 <b>Edmund Optics®</b>		
BFL (AT 587.6nm)	NA	TITLE	550nm 25mm Diameter, OD 2 Shortpass Filter	
ALL DIMS IN	mm	DWG NO	47288	SHEET 1 OF 1

**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**






SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY

SPECIFICATION	VALUE
CUT-OFF WAVELENGTH	600nm±2%
TRANSMISSION BAND	400 - 580nm
REJECTION BAND	625 - 795nm
PASSBAND TRANSMISSION	>85%
REJECTION BAND BLOCKING	≥2.0
CLEAR APERTURE	80%
SURFACE QUALITY	40-20
TRANSMITTED WAVEFRONT	$\lambda/4$ P-V
SLOPE FACTOR	±3%
ANGLE OF INCIDENCE (DEG)	0°
COATING TYPE	Traditional Coated
SUBSTRATE	UV Grade Fused Silica


EFL (AT 587.6nm)	NA	 <b>Edmund Optics®</b>		
BFL (AT 587.6nm)	NA	TITLE	600nm 25mm Diameter, OD 2 Shortpass Filter	
ALL DIMS IN	mm	DWG NO	47289	SHEET 1 OF 1

**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**






SPECIFICATION	VALUE
CUT-OFF WAVELENGTH	650nm $\pm$ 2%
TRANSMISSION BAND	400 - 630nm
REJECTION BAND	675 - 850nm
PASSBAND TRANSMISSION	>85%
REJECTION BAND BLOCKING	$\geq$ 2.0
CLEAR APERTURE	80%
SURFACE QUALITY	40-20
TRANSMITTED WAVEFRONT	$\lambda/4$ P-V
SLOPE FACTOR	$\pm$ 3%
ANGLE OF INCIDENCE (DEG)	0°
COATING TYPE	Traditional Coated
SUBSTRATE	UV Grade Fused Silica

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY


EFL (AT 587.6nm)	NA	 <b>Edmund Optics®</b>		
BFL (AT 587.6nm)	NA	TITLE	650nm 25mm Diameter, OD 2 Shortpass Filter	
ALL DIMS IN	mm	DWG NO	47290	SHEET 1 OF 1

***FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING***



SPECIFICATION	VALUE
CUT-OFF WAVELENGTH	700nm $\pm$ 2%
TRANSMISSION BAND	400 - 680nm
REJECTION BAND	725 - 900nm
PASSBAND TRANSMISSION	>85%
REJECTION BAND BLOCKING	$\geq$ 2.0
CLEAR APERTURE	80%
SURFACE QUALITY	40-20
TRANSMITTED WAVEFRONT	$\lambda/4$ P-V
SLOPE FACTOR	$\pm$ 3%
ANGLE OF INCIDENCE (DEG)	0°
COATING TYPE	Traditional Coated
SUBSTRATE	UV Grade Fused Silica

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

EFL (AT 587.6nm)	NA	 <b>Edmund Optics®</b>		
BFL (AT 587.6nm)	NA	TITLE	700nm 25mm Diameter, OD 2 Shortpass Filter	
ALL DIMS IN	mm	DWG NO	47291	SHEET 1 OF 1