



NOTES:

- SUBSTRATE: N-SF6
- COATING (APPLY ACROSS CLEAR APERTURE)
S1: NONE
S2: NONE
- EDGES: FINE GROUND
- CENTERING: <3 ARCMIN
- ASPHERE FIGURE ERROR: 0.25 μm RMS

△ ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS})^2 * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$




SECTION A-A

COEFFICIENT TABLE △ 6.

COEFFICIENT	S1
SEMI-DIAMETER	1.000000E+01
(1/RADIUS)	4.967710E-02
k	-8.641265E-01
D	0.000000E+00
E	3.151369E-06
F	-1.837155E-09
G	-3.336790E-12
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	25.00	 Edmund Optics®						
SHAPE	CONVEX	PLANO	BFL @ 587.6nm	19.54							
RADIUS	20.130	INFINITY	THIRD ANGLE PROJECTION		TITLE	25mm DIA., 0.50 NUMERICAL APERTURE, UNCOATED, PRECISION ASPHERIC LENS					
SURFACE QUALITY	40-20	40-20									
CLEAR APERTURE	Ø22.50	Ø22.50	ALL DIMS INmm		DWG NO				37428		SHEET 1 OF 1
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED									

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**