



NOTES:

1. SUBSTRATE:
D-ZK3
2. NUMERICAL APERTURE: 0.27
3. COATING
S1 & S2: R(ABS) <1.0% @ 600 - 1050nm
4. FOCAL LENGTH TOLERANCE: ±1%
5. TRANSMITTED WAVEFRONT ERROR (λ , RMS @ 632.8NM): <0.050
6. DESIGN WAVELENGTH: 650NM



SECTION A-A

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	9.85	Edmund Optics®	TITLE LightPath 354306 6.35mm Dia., 0.27 NA, BBAR (600-1050nm), Molded Aspheric Lens	
SHAPE	CONVEX	PLANO	WD	8.40			
SURFACE QUALITY	40-20	40-20	THIRD ANGLE PROJECTION		DWG NO	16686	SHEET 1 OF 1
CLEAR APERTURE	$\phi 5.20$	$\phi 4.57$	ALL DIMS IN	mm			
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					