


NOTES:

1. SUBSTRATE: N-BK7
2. CENTERING TOLERANCE:
BEAM DEVIATION (HALF ANGLE): < 3 arcmin
3. COATING (APPLY ACROSS CLEAR APERTURE)


S1:NONE
S2:NONE

4. EDGES: FINE GROUND

5. ASPHERIC FIGURE ERROR: 0.75 μ m RMS





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

			EFL @ 780nm: 60		 Edmund Optics®		
	S1	S2				TITLE	75mm Dia., 0.63 NA, Uncoated, NIR Aspheric Lens
SHAPE	CONVEX	PLANO					
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE (mm)	Ø69.00	Ø69.00					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	13508	SHEET 1 OF 1