



NOTES:

1. SUBSTRATE: N-BK7
2. CENTERING TOLERANCE:
BEAM DEVIATION (HALF ANGLE): < 3 arcmin
3. COATING (APPLY ACROSS CLEAR APERTURE)

S1:NONE
S2:NONE



4. EDGES: FINE GROUND

5. ASPHERIC FIGURE ERROR: 0.75 μ m RMS



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

			EFL @ 780nm: 200.00		 Edmund Optics®			
	S1	S2				TITLE	100mm Dia., 0.25 NA, Uncoated, NIR Aspheric Lens	
SHAPE	CONVEX	PLANO						
SURFACE QUALITY	40-20	40-20						
CLEAR APERTURE (mm)	Ø92.00	Ø92.00						
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	13511		SHEET 1 OF 1

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**