NOTES:

1. SUBSTRATE MATERIAL: Fused Silica (Corning 7980)

2. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: Rabs ≤1.0% @ 350 - 450nm Rayg ≤1.5% @ 250 - 700nm




ARROW POINTS TOWARDS TILTED SURFACE




FINE GROUND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

6. Rohs Compliant





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
RADIUS	∞	∞
MIN CLEAR APERTURE	Ø22.50	Ø22.50
SURFACE QUALITY	20-10	20-10
SURFACE ACCURACY	λ/10	λ/10
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

		Control Edmund Optics®			
	THIRD ANGLE PROJECTION	HIRD ANGLE TITLE 25mm Dia., UV-VIS Coated, Fused Silica Wedged Window		ica	
)	ALL DIMS IN	mm	DWG NO	17664	SHEET 1 OF 1