



1. SUBSTRATE:
SCHOTT KG2

2. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: NONE


4. DENSITY (g/cm³): 2.52
OPERATING TEMPERATURE (°C): 300 Maximum
REFLECTION FACTOR: 0.92



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	THIRD ANGLE PROJECTION 		TITLE SCHOTT KG2, 12.5mm Dia., 1mm Thick, Colored Glass Heat Absorbing Shortpass Filter		
SHAPE	PLANO	PLANO					
SURFACE QUALITY	60-40	60-40					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	18497	SHEET 1 OF 1