

NOTES:

1. SUBSTRATE: N-SF6

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: NONE
S2: NONE

3. EDGES: FINE GROUND



4. CENTERING: <3 ARCMIN

5. ASPHERE FIGURE ERROR: 0.25µm RMS

6. BLACKENED SURFACE

7. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)


$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



COEFFICIENT TABLE 6.	
COEFFICIENT	S1
SEMI-DIAMETER	1.250000E+01
(1/RADIUS)	6.623393E-02
k	-1.169836E+00
D	0.000000E+00
E	2.137395E-05
F	2.276332E-09
G	-5.697829E-11
H	4.345999E-14
J	0.000000E+00
L	0.000000E+00

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	18.75	 Edmund Optics®	
SHAPE	CONVEX	PLANO	BFL @ 587.6nm	11.27		
RADIUS	15.098	INFINITY			TITLE	25mm DIA., 0.66 NUMERICAL APERTURE, UNCOATED, INKED, HIGH PRECISION ASPHERIC LENS
SURFACE QUALITY	40-20	40-20			DWG NO	37427INK
CLEAR APERTURE	Ø22.50	Ø22.50	ALL DIMS IN	mm		
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				SHEET 1 OF 1