



1. SUBSTRATE:
SCHOTT KG5

2. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: NONE

3. FINE GRIND SURFACE


4. DENSITY (g/cm³): 2.53
OPERATING TEMPERATURE (°C): 300 Maximum
REFLECTION FACTOR: 0.92



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		<div>TITLE</div> <div>SCHOTT KG5, 12.5mm Dia., 1mm Thick, Colored Glass Heat Absorbing Shortpass Filter</div>			
SHAPE	PLANO	PLANO						<div>TITLE</div>
SURFACE QUALITY	60-40	60-40						
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	18502	SHEET 1 OF 1	