

NOTES:

1. SUBSTRATE: N-SF5

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: NONE
S2: NONE

3. EDGES: FINE GROUND



4. CENTERING: <3 ARCMIN

5. ASPHERE FIGURE ERROR: 0.25µm RMS

6. BLACKENED SURFACE

7. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS})^2 * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



COEFFICIENT TABLE 6.

COEFFICIENT	S1
SEMI-DIAMETER	2.500000E+01
(1/RADIUS)	3.964164E-02
k	-1.187653E+00
D	0.000000E+00
E	4.967341E-06
F	4.493814E-10
G	-6.114163E-14
H	-3.368368E-16
J	0.000000E+00
L	0.000000E+00

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	37.50	 Edmund Optics®		
SHAPE	CONVEX	PLANO	BFL @ 587.6nm	24.74			
RADIUS	25.226	INFINITY	<div>THIRD ANGLE PROJECTION</div>		TITLE	50mm DIA., 0.66 NUMERICAL APERTURE, UNCOATED, INKED, HIGH PRECISION ASPHERIC LENS	
SURFACE QUALITY	40-20	40-20			DWG NO	37439INK	
CLEAR APERTURE	Ø45.00	Ø45.00	ALL DIMS IN mm		SHEET 1 OF 1		
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					