

NOTES:

1. SUBSTRATE:
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: VIS (425 - 625nm)
Ravg ≤ 1.5% @ 425 - 675nm

3. EDGES: FINE GROUND

4. CENTERING: ≤ 5

5. ASPHERE FIGURE ERROR: 1.2λ

6.  ROHS COMPLIANT

$$Z(Y) = \frac{\left(\frac{1}{\text{RADIUS}}\right)^2 Y^2}{1 + \sqrt{1 - (1+k) \left(\frac{1}{\text{RADIUS}}\right)^2 Y^2}} + D*Y^2 + E*Y^4 + F*Y^6 + G*Y^8 + H*Y^{10} + J*Y^{12} + L*Y^{14} + M*Y^{16}$$


COEFFICIENT TABLE

COEFFICIENT	S2
RADIUS	77.52
k	-9.600000E-01
D	0.000000E+00
E	1.090400E-07
F	3.438200E-12
G	8.565300E-17
H	3.440300E-21
J	-2.480400E-25
L	0.000000E+00
M	0.000000E+00

	S1	S2
SHAPE	PLANO	CONVEX
RADIUS	INFINITY	77.52
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø 128	Ø 128
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



Edmund Optics®

150mm Dia., 0.50 Numerical Aperture VIS
Coated, Aspheric Lens



ALL DIMS IN

mm

TITLE

DWG NO

22711

SHEET
8 OF 18