





NOTES:

- 1. SUBSTRATE:
Calcium Fluoride (CaF2) Vacuum UV Grade
- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO <1
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: BBAR (2000-5000nm)
- 4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	PLANO	PLANO	<div>THIRD ANGLE PROJECTION</div> 	TITLE	25.4mm Dia. x 3mm Thick, BBAR (2000-5000nm) Coated Calcium Fluoride Window	
SURFACE QUALITY	40-20	40-20		DWG NO	23519	SHEET 13 OF 28
CLEAR APERTURE	Ø 22.86	Ø 22.86		ALL DIMS IN	mm	
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED				