





f': 7 ±0,07

BACK FOCAL LENGTH (BFL): 5,5



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 5,5 CX Øe 6,3 λ AR R(750nm - 800nm, 0°) ≤ 1,50% R(800nm - 1550nm, 0°) ≤ 1,00% Rave(750nm - 1550nm, 0°) ≤ 0,70% 3/ 3 (0,5) λ=632,8 nm 4/ 3,82' 5/ 40 - 20 6/ - P			GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL Øe 6,3 λ AR R(750nm - 800nm, 0°) ≤ 1,50% R(800nm - 1550nm, 0°) ≤ 1,00% Rave(750nm - 1550nm, 0°) ≤ 0,70% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - P		
PROTECTIVE CHAMFERS AS NEEDED				FIRST ANGLE PROJECTION		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 7mm Dia x 7mm FL, NIR II Coated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				DWG NO 71296		
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	SHEET SIZE A4	
			SHEET 1 OF 1			