




f: 50,808 ± 0,51

BACK FOCAL LENGTH (BFL): 44,084



LEFT SURFACE			MATERIAL	RIGHT SURFACE					
R 39,87 CX Øe 49,3 λ AR Rave(600nm - 1050nm, 0°) ≤ 0,50% 3/ 3 (0,5) λ=632,8 nm 4/ 1,27' 5/ 40 - 20 6/ - P			GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL Øe 49,3 λ AR Rave(600nm - 1050nm, 0°) ≤ 0,50% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - P					
PROTECTIVE CHAMFERS AS NEEDED <table><tr><td>ROHS: COMPLIANT</td><td>SCALE: NONE</td><td>λ = 587,6nm</td></tr></table> SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110				ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm	FIRST ANGLE PROJECTION	EO ® Edmund Optics®	
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm							
			TITLE 50,8mm Dia x 50,8079mm FL, NIR I Coated, Plano-Convex Lens						
			ALL DIMS IN: mm	DWG NO 71337	SHEET SIZE A4	SHEET 1 OF 1			