


NOTES:

- 1. SUBSTRATE:
ZERODUR®
- 2. S2 TO BE PARALLEL TO S1 TO WITHIN <30 ARCSEC
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1&S2:
Ravg >98% @ 750 - 1100nm (0 - 45°) Ravg >99% @ 750 - 1100nm (0°)



4. FINE GRIND SURFACE

5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®			
SHAPE	PLANO	PLANO				
SURFACE QUALITY	20-10	COMMERCIAL POLISH				
CLEAR APERTURE	Ø 13.5	N/A				
SURFACE FLATNESS	λ/10	N/A				
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED				
			ALL DIMS IN	mm	TITLE	15mm Dia. 750 - 1100nm Broadband λ/10 ZERODUR® Mirror
			DWG NO			24035
						SHEET 14 OF 18