





f: 76,2 ±0,76

BACK FOCAL LENGTH (BFL): 68,948



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 39,38 CX Øe 49,3 λ AR R(880nm, 0°) ≤ 0,25% Rave(400nm - 870nm, 0°) ≤ 1,25% Rave(890nm - 1000nm, 0°) ≤ 1,25% 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ - 			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 49,3 λ AR R(880nm, 0°) ≤ 0,25% Rave(400nm - 870nm, 0°) ≤ 1,25% Rave(890nm - 1000nm, 0°) ≤ 1,25% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - 		
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110				FIRST ANGLE PROJECTION 	Edmund Optics®	
			ALL DIMS IN: mm	TITLE	50,8mm Dia x 76,1997mm FL, VIS-NIR Coated, Plano-Convex Lens	
				DWG NO	71347	SHEET SIZE A4 SHEET 1 OF 1