





f': 10 ±0,1

BACK FOCAL LENGTH (BFL): 8,1



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 5,17 CX Øe 6,3 λ AR Rave(600nm - 1050nm, 0°) ≤ 0,50% 3/ 3 (0,5) λ=632,8 nm 4/ 5,8' 5/ 40 - 20 6/ - 			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 6,3 λ AR Rave(600nm - 1050nm, 0°) ≤ 0,50% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - 		
PROTECTIVE CHAMFERS AS NEEDED				 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 7mm Dia x 10mm FL, NIR I Coated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN: mm	DWG NO 71302	SHEET SIZE A4	SHEET 1 OF 1