

[All Products](#) / [Lab and Production](#) / [General Tools](#)

Optopolymer® Diffuse Reflecting Film



- Optical PTFE Material with Lambertian Reflection
- High Reflectance from 250 - 2500nm
- High UV Stability and Chemical Resistance

Common Specifications

General

Dimensions (cm):	20 x 30
------------------	---------

Physical & Mechanical Properties

Dimensions (mm):	200 x 300
------------------	-----------



Optical Properties

Wavelength Range (µm):	0.25 - 2.5
------------------------	------------

Environmental & Durability Factors


Operating Temperature (°C):	-200 to +260
-----------------------------	--------------

Technical Information



Typical, normalized reflectance profile of Optopolymer®, showing near Lambertian properties. The gap in data is due to the detector crossing the path of the incident beam.

Optopolymer® Nominal Reflectance



Products

Title	Stock Number	Price	Buy
20 x 30cm Sheet of Optopolymer® Optical PTFE, 0.5mm Thick, Adhesive Film	#22-986	€159,00 Volume Pricing	3 In Stock
20 x 30cm Sheet of Optopolymer® Optical PTFE, 1mm Thick, Adhesive Film	#22-987	€203,00 Volume Pricing	1 In Stock
20 x 30cm Sheet of Optopolymer® Optical PTFE, 2mm Thick, Adhesive Film	#22-988	€246,00 Volume Pricing	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com