

[See all 76 Products in Family](#)

LightPath 354280 | 6.5mm Dia., 0.15 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-113** **9 In Stock**

[Other Coating Options](#)

-

1

+

€85⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€85,00 each
Qty 11-49	€76,50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Thickness: 0.25 (t) (mm) Material: BK7	Compatible Window:
354280	Lightpath Lens Code:
Aspheric Lens	Type:

Typical Applications:	
Collimate or Focus Laser Light	
Physical & Mechanical Properties	
Diameter (mm):	6.50 ±0.020
Clear Aperture CA (mm):	5.5
Edge Thickness ET (mm):	1.78
Center Thickness CT (mm):	2.18 ±0.05
Bevel:	Protective as needed
Distance from Window to Lens (D) (mm):	15.856
Optical Properties	
Effective Focal Length EFL (mm):	18.40 @ 780nm
Numerical Aperture NA:	0.15
Substrate: ☐	D-ZK3
Focal Length Tolerance (%):	±1
Aspheric Design Wavelength (nm):	780
Coating:	BBAR (350-700nm)
Coating Specification:	R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality:	40-20
f/#:	3.33
Wavelength Range (nm):	350 - 700
Working Distance (mm):	17.11
Conjugate Distance:	Infinite
Transmitted Wavefront Error (λ, RMS):	< 0.09
Environmental & Durability Factors	
Operating Temperature (°C):	≤200
Regulatory Compliance	
RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 247:	Compliant

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information



Compatible Mounts