

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

LightPath 354996 | 3mm Dia., 0.30 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock #83-713 3-4 DAYS

[Other Coating Options](#)

1 **€65,00**

ADD TO CART

Qty 1-10

€65,00

Qty 11+

€57,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
3.00 ±0.015

Effective Focal Length EFL (mm):
4.50 @ 633nm

Numerical Aperture NA:
0.30

Substrate: D-ZK3
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 60-40
Clear Aperture CA (mm): 2.70
Edge Thickness ET (mm): 1.33
Center Thickness CT (mm): 1.78 ±0.05
f/#: 1.67
Bevel: Protective bevel as needed
Lightpath Lens Code: 354996
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Working Distance (mm): 3.500
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant