

[See all 7 Products in Family](#)

## 0.50 NA, 4.5mm FL, HOYA Molded Glass Aspheric Lens

See More by [Hoya](#)



HOYA Molded Glass Aspheric Lenses

Stock #13-588 **20+ In Stock**

1  €119<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€119,00 each
Qty 11-49	€94,00 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Aspheric Lens **Type:**

AH10\_Z **Model Number:**

### Physical & Mechanical Properties

**Diameter (mm):**

6.38 +0.00/-0.02

**Clear Aperture CA (mm):**

5.35

**Center Thickness CT (mm):**

2.80

**Bevel:**

Protective as needed

## Optical Properties

**Effective Focal Length EFL (mm):**

4.50 @ 780nm

**Numerical Aperture NA:**

0.50

**Substrate:** □

M-LAF81

**Aspheric Design Wavelength (nm):**

830

**Coating:**

BBAR (805 - 855nm)

**Coating Specification:**

$R_{avg} < 1.5\%$  @ 805 - 855nm (theoretical per surface)

**f/#:**

0.71

**Wavelength Range (nm):**

805 - 855

**Working Distance (mm):**

2.16

**Conjugate Distance:**

0

**Transmitted Wavefront, RMS @ 632.8nm:**

0.052λ

## Regulatory Compliance

**Certificate of Conformance:**

[View](#)

## Product Details

- Precision Glass Molded Lenses
- Compact Sizes for Integration into Measurement Systems
- Multiple Glass Substrates Available

HOYAMolded Glass Aspheric Lenses are used in applications that require lenses with small sizes and high transmission that correct for spherical aberration. These aspheric lenses are manufactured through a patented molding process that produces precision aspheric surfaces to minimize wavefront error. Their small diameters and thicknesses allow for these molded aspheric lenses to be integrated into measurement systems, biomedical instrumentation, or other optical tools. HOYAMolded Glass Aspheric Lenses are available in multiple glass types that offer higher refractive indices and lower dispersion than other molded glass aspheric lens offerings.