

[See all 76 Products in Family](#)

# LightPath 354340 | 6.33mm Dia., 0.64 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-161** **20+ In Stock**

[Other Coating Options](#)

-

1

+

€85<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | €85,00 each                   |
| Qty 11-49      | €76,50 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

| General                                  |                      |
|------------------------------------------|----------------------|
| Thickness: 1.20 (t) (mm)<br>Material: K3 | Compatible Window:   |
| 354340                                   | Lightpath Lens Code: |
| Aspheric Lens                            | Type:                |

|                                        |  |
|----------------------------------------|--|
| Typical Applications:                  |  |
| Collimate or Focus Laser Light         |  |
| Physical & Mechanical Properties       |  |
| Diameter (mm):                         |  |
| 6.33 ±0.020                            |  |
| Clear Aperture CA (mm):                |  |
| 5.1                                    |  |
| Edge Thickness ET (mm):                |  |
| 1.48                                   |  |
| Center Thickness CT (mm):              |  |
| 3.10 ±0.03                             |  |
| Bevel:                                 |  |
| Protective as needed                   |  |
| Distance from Window to Lens (D) (mm): |  |
| 1.483                                  |  |
| Optical Properties                     |  |
| Effective Focal Length EFL (mm):       |  |
| 4.03 @ 685nm                           |  |
| Numerical Aperture NA:                 |  |
| 0.64                                   |  |
| Substrate: <input type="checkbox"/>    |  |
| <a href="#">D-ZK3</a>                  |  |
| Focal Length Tolerance (%):            |  |
| ±1                                     |  |
| Aspheric Design Wavelength (nm):       |  |
| 685                                    |  |
| Coating:                               |  |
| BBAR (350-700nm)                       |  |
| Coating Specification:                 |  |
| R <sub>avg</sub> ≤0.5% @ 350 - 700nm   |  |
| Surface Quality:                       |  |
| 40-20                                  |  |
| f/#:                                   |  |
| 0.78                                   |  |
| Wavelength Range (nm):                 |  |
| 350 - 700                              |  |
| Working Distance (mm):                 |  |
| 2.68                                   |  |
| Conjugate Distance:                    |  |
| Infinite                               |  |
| Transmitted Wavefront Error (λ, RMS):  |  |
| < 0.08                                 |  |
| Environmental & Durability Factors     |  |
| Operating Temperature (°C):            |  |
| ≤200                                   |  |
| Regulatory Compliance                  |  |
| RoHS 2015:                             |  |
| <a href="#">Compliant</a>              |  |
| Certificate of Conformance:            |  |
| <a href="#">View</a>                   |  |
| Reach 247:                             |  |
| <a href="#">Compliant</a>              |  |

## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



## Technical Information



;