


TECHSPEC[®] 0.5mm Diameter, Fused Silica Ball Lens



Stock #67-379 20+ In Stock

-

1

+

€60^{.50}

ADD TO CART

Volume Pricing	
Qty 1-10	€60,50 each
Qty 11-49	€48,25 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads	
General	
Ball Lens	Type:
Physical & Mechanical Properties	
0.50	Diameter (mm):
±2.5	Diameter Tolerance (µm):

Optical Properties

Fused Silica (Corning 7980)		Substrate: ☐
Uncoated		Coating:
200 - 2200	Wavelength Range (nm):	
1.458	Index of Refraction (n _d):	
0.625	Sphericity (μm):	

Regulatory Compliance

Compliant		RoHS 2015:
View		Certificate of Conformance:
Compliant		Reach 247:

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Excellent UV Transmission
- Low Coefficient of Thermal Expansion
- Ball and Half-Ball Options Available

TECHSPEC® Fused Silica Ball and Half-Ball Lenses feature high transmission from 200nm to 2.2μm with a low coefficient of thermal expansion, making it ideal for the most demanding ball lens applications in the ultraviolet, visible, and near-infrared spectra. Ball lenses are commonly used for improving signal coupling between fibers, emitters, and detectors, as well as objective lenses in endoscopy and bar-code scanning applications. Half-ball lenses simplify handling and integration. TECHSPEC Fused Silica Ball and Half-Ball Lenses are uncoated with a fused silica substrate. The lenses are available in diameters ranging from 0.50 to 5.00mm.

Technical Information



UV FS Transmission Curve

