

0.62 NA, 3.10mm FL, RPO VIS Molded Glass Aspheric Lens



Stock **#73-665** 20+ In Stock

-

1

+

€93^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€93,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Aspheric Lens

Type:

Physical & Mechanical Properties

6.33 ±0.015

Diameter (mm):

5.40

Clear Aperture CA (mm):

3.19

Center Thickness CT (mm):

Protective as needed		Bevel:
Optical Properties		
3.10	Effective Focal Length EFL (mm):	
0.62	Numerical Aperture NA:	
H-ZLaF52	Substrate: ☐	
633	Aspheric Design Wavelength (nm):	
BBAR (400 - 600nm)	Coating:	
R _{avg} <1% @ 400 - 600nm	Coating Specification:	
60-40	Surface Quality:	
0.49	f/#:	
400 - 600	Wavelength Range (nm):	
1.76	Working Distance (mm):	
Regulatory Compliance		
View	Certificate of Conformance:	

Product Details

- Precision Visible Glass Molded Lenses
- Ideal for High Volume Production Requirements
- Multiple Glass Substrates Available

Rochester Precision Optics (RPO) Visible Molded Glass Aspheric Lenses offer several key benefits, including high precision, >99% transmission, and improved performance by reducing optical aberrations, leading to smaller spot sizes and sharper images. Cost-effective molding processes enable options for high-quantity OEM integration while maintaining consistent specifications. Rochester Precision Optics (RPO) Visible Molded Glass Aspheric Lenses are available with various focal lengths and numerical apertures and are AR coated for >99% transmission from 400 - 600nm. Their lightweight form factor, small diameter, and reduced thickness allow these molded aspheric lenses to be integrated into cameras, aerospace systems, measurement systems, biomedical instrumentation, and handheld optical tools.