

0.9mW 655nm, Micro LDM Laser Diode



Stock #57-100 **10 In Stock**

- 1 + €143^{.00}

ADD TO CART

Volume Pricing

Qty 1-9	€143,00 each
Qty 10+	€136,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

Mean Time To Failures MTTF @ 25° (hours):
≥50,000

Note:
Includes: Users Manual, Warning Label, and Focus Key

Type of Laser:
Diode

Physical & Mechanical Properties

3 Weight (g):

<25 Pointing Accuracy (mrad):

220 Length of Leads (mm):

27.40 Length (mm):

Optical Properties

655.00 Wavelength (nm):

<40 Beam Size at Nearest Focus (μm):

3 x 1 at Aperture Beam Diameter (mm):

<0.5 Beam Divergence (mrad):

Red Color:

50mm - ∞ Focus Range (mm):

Electrical

<20 Operating Current (mA):

0.9 Output Power (mW):

± 5 at 25°C Output Power Tolerance (%):

Hardware & Interface Connectivity

Power Supply:
Power Supply Required and Sold Separately:
USA: [#59-099](#)
Europe: Not Available
Japan: [#59-099](#)
Korea: [#33-771](#)
China: [#59-099](#)

3.5 - 5 VDC Power Requirement:

red (+), black (-) Electrical Leads/ Pin Connections:

Free Space Output Type:

Environmental & Durability Factors

-10 to +45 Operating Temperature (°C):

-10 to +85 Storage Temperature (°C):

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 240:

Product Details

- 7mm Housing Diameter
- Focusable
- Low Voltage DC Operation
- Reverse Polarity Protection

Micro LDMLaser Diode Modules feature an extremely compact design that includes automatic power control circuits and focusable optics. The rugged body is low voltage isolated from the drive electronics, removing the need for negative or floating supplies. It has a highly visible red laser output that can be seen in most daylight conditions. Micro LDMLaser Diode Modules' additional features include aspheric lens, elliptical beam, small output beam diameter, and focused spot size. Meet IEC60825 certification, in accordance with CDRH. Applications include alignment/positioning, bar code readers, dimensional scanning, metrology, event detection, robot control, target designation, edge detection, analysis, and security.

Recommended power supply: [#59-099](#)

