


0° AOI 25mm Dia, Cold Mirror



Stock #43-844 CLEARANCE 20+ In Stock

€15²⁵

ADD TO CART

Volume Pricing

Qty 1+	€15,25 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Cold Mirror Type:

Physical & Mechanical Properties

25.00 Diameter (mm):

3.30 Thickness (mm):

±0.25 Dimensional Tolerance (mm):

Optical Properties

Dielectric **Coating Type:**

Cold Mirror, 0° **Coating:**

4 - 6λ **Surface Flatness (P-V):**

425 - 1200 **Wavelength Range (nm):**

BOROFLOAT® **Substrate:** □

0.00 **Angle of Incidence (°):**

Coating Specification:
R_{avg} >90% @ 425 - 675nm
T_{avg} >85% @ 800 - 1200nm

80-50 **Surface Quality:**

Regulatory Compliance



[View](#) **Certificate of Conformance:**

Product Details

- 0° and 45° Angle of Incidence Options Available
- Reflects 90% of Visible Light
- Transmits 80% of the NIR and IR

These Cold Mirrors have a 0° and 45° angle of incidence and are ideal for decreasing the undesirable heat caused by infrared radiation. A multi-layer dielectric coating reflects 90% of visible light while transmitting over 80% of the NIR and IR. Cold Mirrors function satisfactorily with resistance to damage from ambient temperatures of -45°C to +232°C and are ideal for projection systems, where heat build-up can lead to system damage. Made of BOROFLOAT® glass, these Cold Mirrors can be cut to the desired size for any application.

Technical Information



Compatible Mounts