

# 1" Travel, 2.62"L x 2.62"W Ball Bearing Slide



Linear Motion Ball Bearing Slides



Stock **#37-356** **5 In Stock**

-

1

+

€313<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €313,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English

Type:

Physical & Mechanical Properties

Linear (X)

Type of Movement:

Guide System:

|                                                                      |                              |
|----------------------------------------------------------------------|------------------------------|
| Ball Bearing                                                         |                              |
| 66.5 x 66.5                                                          | Stage Size (mm):             |
| 1                                                                    | Travel (inches):             |
| Construction:<br>Aluminum Top and Base/440C Stainless Steel Bearings |                              |
| 1.00                                                                 | Height (inches):             |
| 40.0                                                                 | Load Capacity, Normal (lbs): |
| (2) #1/4 on Base                                                     | S.H.C.S. C'bore:             |

|                        |                                  |
|------------------------|----------------------------------|
| 2.62 x 2.62            | Stage Size (inches):             |
| 0.00008/inch of travel | Straight Line Accuracy (inches): |

|     |               |
|-----|---------------|
| 0.6 | Weight (lbs): |
|-----|---------------|

Hardware & Interface Connectivity

|        |                |
|--------|----------------|
| Manual | Type of Drive: |
|--------|----------------|

Threading & Mounting

|                  |                   |
|------------------|-------------------|
| (8) 10-32 on Top | Mounting Threads: |
|------------------|-------------------|

Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |


Product Details

- High Straight Line Accuracy
- Low Wear, Low Friction Sliding Motion
- Preloaded to Eliminate Wobble and Unwanted Play


Linear Motion Ball Bearing Slides are mechanically simple linear motion devices comprised of a stationary base with a mobile carriage riding on top. One row of hardened steel balls on each side of the base provides the accurate, low-friction sliding motion between the stationary base and the top slide. Each row of bearings is contained between two hardened, precision steel rods. Linear Motion Ball Bearing Slides are preloaded to eliminate wobble and unwanted play in the system. Ball slides are functionally much more reliable than dovetail slides since there is no direct sliding contact between the top and bottom pieces. The slides also eliminate the rapid wear problems, regular lubrication requirements, and the skipping/jumping (caused by the increased force needed to initiate movement) that are characteristic of dovetail assemblies.

Technical Information

| Dimensions (Inches) |      |      |      |      |      |      | Base Mounting Holes |      |      | Top Mounting Holes |      |       |    | Stock No. |
|---------------------|------|------|------|------|------|------|---------------------|------|------|--------------------|------|-------|----|-----------|
| Fig.                | A    | B    | C    | D    | E    | F    | G                   | H    | J    | K                  | L    | M     | N  |           |
| B                   | 0.59 | 1.12 | 0.32 | 0.24 | 0.24 | 1    | 0.19                | 0.75 | #2   | 0.218              | 0.63 | 2-56  | 4  | #53-849   |
| B                   | 0.59 | 2.12 | 0.32 | 0.24 | 0.24 | 1    | 0.37                | 1.38 | #2   | 0.218              | 1.63 | 2-56  | 4  | #53-850   |
| B                   | 1.00 | 1.68 | 0.50 | 0.36 | 0.36 | 1    | 0.22                | 1.25 | #4   | 0.438              | 1.25 | 6-32  | 4  | #53-853   |
| A                   | 2.62 | 2.62 | 1.00 | 1.48 | 0.61 | -    | 0.31                | 2.00 | #1/4 | -                  | 2.00 | 10-32 | 8  | #37-356   |
| B                   | 1.75 | 3.00 | 0.75 | 0.88 | 0.40 | 5.00 | 0.31                | 2.38 | #6   | 1.000              | 0.50 | 6-32  | 12 | #37-361   |



Units: Inches



Units: Inches

| Type     | A   | B     | C     | D  | E | F    | G  | Stock No.               |
|----------|-----|-------|-------|----|---|------|----|-------------------------|
| Figure A | 4"  | 0.69" | 0.5"  | 6  | - | -    | -  | <a href="#">#37-363</a> |
| Figure A | 5"  | 1.19" | 1"    |    |   |      |    | <a href="#">#37-364</a> |
| Figure A | 6"  | 1.69" | 0.5"  | 10 | 1 |      |    | <a href="#">#37-365</a> |
| Figure B | 9"  | 2"    | 3.5"  | 3  | 3 | 1.5" | 8  | <a href="#">#37-366</a> |
| Figure B | 12" |       | 5"    |    | 5 | 1"   | 12 | <a href="#">#37-367</a> |
| Figure B | 15" | 4"    | 3.25" | 5  | 6 | 1.5" | 14 | <a href="#">#37-368</a> |
| Figure B | 18" |       | 4"    |    | 8 | 1"   | 18 | <a href="#">#37-369</a> |

