

[See all 33 Products in Family](#)

10 x 10mm, 300µm Pitch, 10.1° Div., Cyl. Microlens Array UV-VIS



Stock #72-600 **1 In Stock**

- 1 + €765^{.00}

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | €765,00 each |
| Qty 11+ | €617,00 each |
| Need More? | Request Quote |

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Lens Array **Type:**

Physical & Mechanical Properties

10.0 x 10.0 ±0.05 **Dimensions (mm):**

0.380 **Radius R (mm):**

1.20 ±0.05 **Thickness (mm):**

Optical Properties

0.80 **Effective Focal Length EFL (mm):**

Fused Silica (Corning 7980) **Substrate:** □

UV-NIR (250-700nm) **Coating:**

250 - 700 **Wavelength Range (nm):**

Coating Specification:
R_{abs} ≤1.0% from 350 - 450nm @ 0° AOI
R_{avg} ≤1.5% @ 250 - 700nm @ 0°

±10.1 **Divergence Angle (°):**

300.00 ±0.25 **Pitch (µm):**

Single-Sided **Array Type:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 250:**

Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.