

10 x 10mm Broadband Hybrid Diffuser



Broadband Hybrid Diffusers

Stock #36-609 **20+ In Stock**

⊖ 1 ⊕ €40²⁵

ADD TO CART

Volume Pricing	
Qty 1-10	€40,25 each
Qty 11-49	€32,25 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Opal Diffuser **Type:**

Physical & Mechanical Properties

10.00 x 10.00 ±0.3 **Dimensions (mm):**

120 **Crit:** □

1.75 ±0.1	Thickness (mm):
10.00	Width (mm):
10.00	Length (mm):
Optical Properties	
Uncoated	Coating:
White Diffusing Glass	Substrate: <input type="checkbox"/>
400 - 1100	Wavelength Range (nm):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 211:
View	Certificate of Conformance:

Product Details

- Surface Treated Semi-Opaque White Glass
- Two Mechanisms of Scatter
- Excellent Scattering into the NIR

Broadband Hybrid Diffusers are semi-opaque diffusers designed to scatter efficiently from the UV to the NIR. Featuring surfaces sandblasted with 120-grit and a 1.75mm thick scattering medium, these diffusers uniquely offer two mechanisms of scatter. Each scatter mechanism has its own wavelength dependency, and when combined on a single optic, produce a diffuser that scatters across a wide spectral region. Broadband Hybrid Diffusers are ideal for applications that require high scatter for even illumination and can be used as view screens.

Compatible Mounts

;