

TECHSPEC® 100mm Dia., 0.63 Numerical Aperture Uncoated, Aspheric Lens



Stock **#15-003** 3-4 DAYS

[Other Coating Options](#)

- 1 + **€950,00**

ADD TO CART

Qty 1-5
€950,00

Qty 6+
€760,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
100.00 +0.0/-0.1

Effective Focal Length EFL (mm):
80.00 @ 587.6nm

Numerical Aperture NA:

0.63
Back Focal Length BFL (mm): 61.35
Substrate: ☐ N-SF5
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 90
Edge Thickness ET (mm): 5.78
Center Thickness CT (mm): 31.20 ±0.1
f#: 0.80
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 380 - 2500
Conjugate Distance: Infinite
Power (diopters): 12.50

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View