


[See all 3 Products in Family](#)

100µm Emitter, 500µm Pitch Slow Axis Collimator



Slow Axis Collimators

Stock **#88-404** **6 In Stock**

⊖ 1 ⊕ €202⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€202,00 each
Qty 11-49	€182,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Beam Shaper

Type:

Physical & Mechanical Properties

11.0 x 1.4 **Clear Aperture CA (mm):**

100.00 **Emitter Size (µm):**

1.50	Height (mm):
0.05	Height Tolerance (mm):
12.00	Length (mm):
±0.05	Length Tolerance (mm):
0.55	Width (mm):
0.01	Width Tolerance (mm):

Optical Properties

2.88	Effective Focal Length EFL (mm):
S-TIH53	Substrate: <input type="checkbox"/>
7.69	f#:
0.07	Numerical Aperture NA:
BBAR (790-990nm)	Coating:
790 - 990	Wavelength Range (nm):
2.58	Back Focal Length BFL (mm):
R _{avg} <1.0% @ 790 - 990nm	Coating Specification:
500.00	Pitch (µm):
M4	Surface Accuracy:
>99	Transmission (%):
40.00	Divergence 1/e ² (mrad):


Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 197:
View	Certificate of Conformance:

Product Details

- Designed for Use with Laser Bars
- Can be Used With [Fast Axis Collimators](#)
- Low Curvature Deviation for Increased Collimation
- [Fast Axis Collimators](#) Also Available

Slow Axis Collimators consist of a monolithic array of cylindrical lenses designed to collimate the individual emitters of a laser bar. Slow Axis Collimators feature greater than 99% transmission across the designated spectral range to guarantee high performance with minimal loss of light. To meet an application's unique collimation needs, Slow Axis Collimators can also be used with Fast Axis Collimators for custom collimation combinations.



Technical Information

