

# 100mm Dia. Broadband Hybrid Diffuser



Broadband Hybrid Diffusers

Stock **#36-617** 20+ In Stock

-

1

+

€89<sup>.50</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | €89,50 each                   |
| Qty 11-49      | €71,50 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Opal Diffuser

Type:

Physical & Mechanical Properties

100.00 ±0.5

Diameter (mm):

120

Grit:

|                       |                                     |
|-----------------------|-------------------------------------|
| 1.75 ±0.1             | Thickness (mm):                     |
| Optical Properties    |                                     |
| Uncoated              | Coating:                            |
| White Diffusing Glass | Substrate: <input type="checkbox"/> |
| 400 - 1100            | Wavelength Range (nm):              |
| Regulatory Compliance |                                     |
| Compliant             | RoHS 2015:                          |
| Compliant             | Reach 211:                          |
| View                  | Certificate of Conformance:         |

## Product Details

- Surface Treated Semi-Opaque White Glass
- Two Mechanisms of Scatter
- Excellent Scattering into the NIR

Broadband Hybrid Diffusers are semi-opaque diffusers designed to scatter efficiently from the UV to the NIR. Featuring surfaces sandblasted with 120-grit and a 1.75mm thick scattering medium, these diffusers uniquely offer two mechanisms of scatter. Each scatter mechanism has its own wavelength dependency, and when combined on a single optic, produce a diffuser that scatters across a wide spectral region. Broadband Hybrid Diffusers are ideal for applications that require high scatter for even illumination and can be used as view screens.

## Compatible Mounts