

TECHSPEC<sup>®</sup> 100mm Dia. Linear Plastic Polarizer (XP42-200)



Stock **#86-202** **8 In Stock**

-

1

+

€105<sup>,00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €105,00 each                  |
| Qty 6-49       | €83,80 each                   |
| Qty 50-99      | €78,80 each                   |
| Need More?     | <a href="#">Request Quote</a> |

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer

Type:

Physical & Mechanical Properties

100.00 ±1.0

Diameter (mm):

2.22 ±0.25

Thickness (mm):

|                                               |                                     |
|-----------------------------------------------|-------------------------------------|
| Polarizing Film on PMMA                       | Construction:                       |
| Optical Properties                            |                                     |
| 9000:1                                        | Extinction Ratio:                   |
| <a href="#">XP42-200 on PMMA</a>              | Substrate: <input type="checkbox"/> |
| Single: 42<br>Parallel: 36<br>Crossed: <0.004 | Transmission (%):                   |
| 400 - 700                                     | Wavelength Range (nm):              |
| >99.98                                        | Polarization Efficiency (%):        |
| Environmental & Durability Factors            |                                     |
| -40 to +80                                    | Operating Temperature (°C):         |
| Regulatory Compliance                         |                                     |
| <a href="#">Compliant</a>                     | RoHS 2015:                          |
| <a href="#">View</a>                          | Certificate of Conformance:         |
| <a href="#">Compliant</a>                     | Reach 235:                          |

## Product Details

- Excellent Extinction Ratio of 9000:1
- Increased Durability through Lamination on PMMA
- High Transmission of Unpolarized Light from 400 – 700nm

TECHSPEC® High Contrast Plastic Linear Polarizers (XP42-200 & XP42-300) are ideal for a variety of imaging applications. Offered in multiple sizes, these linear polarizers feature an excellent extinction ratio and high transmission of unpolarized light from 400 – 700nm. The plastic substrate results in a lightweight polarizer, ideal for weight constrained applications. TECHSPEC® High Contrast Plastic Linear Polarizers (XP42-200 & XP42-300) offer increased durability compared to [polarizing film](#).

When unpolarized light enters a linear polarizer, the light that is polarized perpendicular to the polarization axis is absorbed, and light parallel to the polarization axis is transmitted. TECHSPEC® High Contrast Plastic Linear Polarizers (XP42-200) utilize a stretched PVA film to create the polarization axis. To increase durability, the film is then laminated between two plastic plates.

**Note:** These linear polarizers are not recommended for laser applications.

### Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Plastic Linear Polarizers (XP42-200) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

## Technical Information

