

[All Products](#) / [Lights and Illuminators](#) / [CCS High Intensity Ring Lights](#)

[See all 17 Products in Family](#)

100mm High Power Ring Light (Model #21-804-RCD-05P)

See More by [CCS](#)



Stock #21-804-RCD-05P **RECERTIFIED** 1 In Stock

- 1 +

€950⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€950,00 each
Need More?	Request Quote

Product Downloads
EO Spec Sheet

! Prices shown are exclusive of VAT/local taxes

General

Model Number:	HPR2-100FC	Type of Illumination:	LED Illuminator
Note:	For RGB intensity control, use controller #19-970 Requires #20-175, #20-171 or #19-970 for Power	Manufacturer:	CCS
Geometry:	Ring Light	Illumination Mode:	Constant

Physical & Mechanical Properties

Dimensions (mm):	OD: 116, ID: 66, Height 26.4	Weight (g):	168
-------------------------	------------------------------	--------------------	-----

Optical Properties

Color:	RGB	Wavelength:	Red: 622nm, Green: 525nm, Blue: 470nm
---------------	-----	--------------------	---------------------------------------

Electrical

Power Consumption (W):	11
-------------------------------	----

Hardware & Interface Connectivity

Input Voltage (V): 24

Power Supply: Power Supply Required and Sold Separately:
USA: [#73-491](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Regulatory Compliance

Certificate of Conformance: [View](#)

Product Details

- Uniform High Intensity Diffuse Light Source
- Switchable Red, Green, Blue, and White Channel Outputs
- Illumination for Text Recognition (OCR) and Color Examination Applications

CCS High Intensity Ring Lights feature a curved diffusion plate which provides uniform high intensity diffuse light. These lights can be used for a wide range of working distances as the unique design ensures little change in the uniform region as distance from the workpiece increases or decreases. The full color models feature independently controllable channels of red, green, and blue LED's while single color red, blue, and white models are also available. CCS High Intensity Ring Lights are ideal for a wide variety of detection applications such as text recognition (OCR) and color examination.

3D-Printable Mount Files



Ring Light Configuration

[Download Now](#)

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to ¼-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



Application Note

Illumination Mounts for Machine Vision Applications
[Read >>](#)





Video

Assembly of 3D Printed Mounts for Common Illumination Geometries
[Watch >>](#)

Technical Information

Accessories

Note: Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
MORE+	24V Power Supply with Tinned Leads		#66-855	€95,00 Request Quote	6 In Stock <input type="text" value="1"/> 
MORE+	Advanced Digital Controller, 24V, 3 Channels		#19-970	€1.045,00 Request Quote	CONTACT US <input type="text" value="1"/> 

	Title	Compare	Stock Number	Price	Buy
--	-------	---------	--------------	-------	-----

MORE+

24V Power Supply with FCB Cable

#73-491

€136,00

CONTACT US

1



Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: