

[See all 8 Products in Family](#)

100mm² DUV Photodiode with Ceramic Housing



DUVPhotodiodes

Stock **#84-986** [CONTACT US](#)

⊖ 1 ⊕ €222.⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-4 | €222,00 each |
| Qty 5-9 | €197,00 each |
| Qty 10-24 | €174,00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

3 @ 0 V, 1 kΩ **Rise Time (μs):**

Physical & Mechanical Properties

10.0 x 10.0 **Size of Active Area (mm):**

Active Area (mm²):

100.0

Optical Properties

980.00 **Peak Response Wavelength (nm):**

Electrical

0.5 **Responsivity @ 980nm (AW):**

Minimum: 0.04
Typical: 0.2 **Shunt Resistance @ V=-10mV (GΩ):**

0.34 **Responsivity @ 633nm (AW):**

0.12 **Responsivity @ 200nm (AW):**

1100.00 **Capacitance @ V_R=0V (pF):**

8.2×10^{-14} **Noise Equivalent Power NEP (W/ Hz^{1/2}):**
@ 0 V, 200nm

5.00 **Maximum Reverse Voltage (V):**

Hardware & Interface Connectivity

Ceramic **Connector:**

Environmental & Durability Factors

-20 to +60 **Operating Temperature (°C):**

-20 to +80 **Storage Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Excellent UV Sensitivity
- High Shunt Resistance
- Low Capacitance

DUV Photodiodes are ideal for a wide variety of applications, including UV spectrophotometry and analytical and medical instrumentation. DUV Photodiodes are designed for enhanced responsivity from 200 – 400nm, and with sensitivity extending down to 190nm. DUV Photodiodes feature quartz windows and either metal or ceramic housing. Models with suppressed NIR performance are also available.