

TECHSPEC[®] 102.3mm Dia x 1524.7mm FL Achromatic Lens



Stock **#50-107** 6 In Stock

-

1

+

€1.410^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	€1.410,00 each
Qty 6-25	€1.200,00 each
Qty 26-49	€1.130,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Lens

Type:

Physical & Mechanical Properties

102.31 +0.00/-0.12

Diameter (mm):

98.75

Clear Aperture CA (mm):

5.00	Centering (arcmin):
12.37	Center Thickness CT 1 (mm):
8.76	Center Thickness CT 2 (mm):
-2169.77	Radius R ₄ (mm):
19.18	Edge Thickness ET (mm):
Unmounted, Airspaced 0.10mm	Construction:
Protective as needed	Bevel:

Optical Properties	
1,524.73	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
1514.53	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
908.13	Radius R ₁ (mm):
-626.59	Radius R ₂ (mm):
-625.40	Radius R ₃ (mm):
N-BK7 / N-SF2	Substrate: ☐
60-40	Surface Quality:
14.9	f/#:
0.03	Numerical Aperture NA:
MgF ₂ (400-700nm)	Coating:
R _{avg} ≤1.75% @ 400 - 700nm	Coating Specification:
400 - 700	Wavelength Range (nm):


Regulatory Compliance	
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Offered in Cemented or Air-Spaced Designs
- Mounted Versions Available for Easy Integration
- Feature MgF₂ Anti-Reflection Coating

TECHSPEC® Large Precision Achromatic Lenses offer near-diffraction limited performance across the designated wavelength range. These color-corrected achromatic lenses feature long focal lengths and are available in either cemented or air-spaced designs. The lenses have a MgF2 anti-reflection coating and are available in diameters up to 140mm. TECHSPEC® Large Precision Achromatic Lenses, in the mounted version, feature a male mounting thread for easy integration into optical systems. Adhesive foil spacers and mounting instructions are included for unmounted, air-spaced achromatic lenses.

Technical Information



Coating Curves

;