


[See all 32 Products in Family](#)

# 1064nm, 18-23mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal πShaper\_1064\_Q-20

See More by [AdiOptica](#)



Focal Flat Top Beam Shaper



Stock #12-237 **1 In Stock**

€2.830<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	€2.830,00 each
Qty 5-10	€2.545,00 each
Qty 11+	€2.410,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

## Product Downloads

## General

Model Number:  
πShaper\_1064\_Q-20

Beam Shaper	Type:
<a href="#">#12-323</a>	Compatible Adapter:
Physical & Mechanical Properties	
21.00	Length (mm):
70	Weight (g):
38	Clear Aperture CA (mm):
64.00	Diameter (mm):
18 - 23	Input Beam Diameter, $1/e^2$ (mm):
Optical Properties	
>99	Transmission (%):
1064	Design Wavelength DWL (nm):
1020 - 1100	Wavelength Range (nm):
TEM <sub>00</sub>	Input Beam Mode:
<1.5	Typical Input Beam Mode Quality, M <sup>2</sup> :
±20	Input Beam Divergence (mrad):
Electrical	
0.4	Maximum Input Power, CW (kW):
Threading & Mounting	
M58 x 1	Inner Thread:
M58 x 1	Outer Thread:
Regulatory Compliance	
<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	Reach 250:

## Product Details

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica πShaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal-πShaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal-πShapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

## Technical Information

