

[All Products](#) / [Laser Optics](#) / [Laser Optics](#) / [Jenoptik JENar™ Silverline™ F-Theta](#)

[See all 12 Products in Family](#)

# 103mm, 355nm

See More by [Jenoptik](#)



Stock #16-768 [CONTACT US](#)

- 1 +

€2.725<sup>,00</sup>

**ADD TO CART**

Volume Pricing	
Qty	€2.725,00
1+	each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

Product Downloads	
STEP:step	PDF Drawing:pdf
IGES:igs	Spec Sheets:pdf
Zemax:zar	eDrawing:eprt
Code V:seq	EO Spec Sheet
<a href="#">Download All</a>	

## General

<b>Model Number:</b>	017700-402-26	<b>Type:</b>	JENar Silverline F-Theta
<b>Note:</b>	Damage Warning: Not recommended for picosecond and femtosecond laser pulses.	<b>Protective Window:</b>	#17-690: One Included
<b>Manufacturer:</b>	Jenoptik		

## Physical & Mechanical Properties

<b>Maximum Diameter (mm):</b>	99.8 +0/-0.1	<b>Weight (g):</b>	700
<b>X/Y Mirror Angle (°):</b>	±7.2	<b>Flange Distance (mm):</b>	176.95
<b>Input Beam Diameter, 1/e<sup>2</sup> (mm):</b>	9	<b>Maximum Length (mm):</b>	66.5

## Optical Properties

<b>Focal Length FL (mm):</b>	103.00	<b>Substrate:</b>	<b>Fused Silica</b> (Corning 7980)
<b>Scan Angle (°):</b>	±20.1	<b>Scan Field (mm):</b>	50 x 50
<b>Telecentricity (°):</b>	F-Theta Only: 2.40 With Scanner: 2.80	<b>Working Distance (mm):</b>	134.85
<b>Wavelength Range (nm):</b>	355	<b>Damage Threshold, By Design:</b>	1.0 J/cm <sup>2</sup> * (τ/[ns]) <sup>0.40</sup> 1.0 MW/cm <sup>2</sup>

<b>Scan Field Diameter (mm):</b>	71	<b>Focus Size Diameter, 1/e<sup>2</sup> (μm):</b>	8
<b>GDD Specification (fs<sup>2</sup>):</b>	5670	<b>Damage Threshold, CW:</b>	1.0 MW/cm <sup>2</sup> *

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

**Select Your Country/Region:**

### Threading & Mounting

<b>Mounting Threads:</b>	M85 x 1
--------------------------	---------

### Regulatory Compliance

<b>Certificate of Conformance:</b>	<a href="#">View</a>
------------------------------------	----------------------

## Product Details

- Low-Absorption Fused Silica Substrates for High-Power Laser Applications
- Large Scan Fields Up to 328mm x 328mm
- High Damage Thresholds and Low Telecentricity Errors
- [Jenoptik JENar™ F-Theta Scanning Lenses](#) Also Available

Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses provide flat field at the image plane and feature low-absorption fused silica substrates, making them suitable for high-power laser applications. These F-Theta lenses offer high damage thresholds to handle beam powers of up to four kilowatts without active cooling and are available in various wavelengths ranging from 266nm to 1100nm. With large processing areas up to 328mm x 328mm, low telecentricity errors, and diffraction-limited image quality, these lenses allow for high spot consistency and increased throughput over the entire scanning range. With their patented stackable mounting technology, these lenses compensate for thermal stresses and improve the stability of the optical components, ensuring high-precision adjustment and position control in OEM systems. Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses were specially developed for applications requiring high-power and short-pulse Nd:YAG, Yb:doped, and fiber laser sources and are used in conjunction with [galvanometers](#) and [beam expanders](#).

Contact us if your application requires [Jenoptik JENar™ F-Theta Scanning Lenses](#) or Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses not shown on our website.

## Accessories

**Note:** Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
<a href="#">MORE+</a>	Protective Window for #16-768		<a href="#">#17-690</a>	€310,00 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> 1
<a href="#">MORE+</a>	Protective Window for #16-769 and #16-770		<a href="#">#17-693</a>	€545,00 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> 1
<a href="#">MORE+</a>	Protective Window for #17-021 and #17-022		<a href="#">#17-694</a>	€830,00 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> 1
<a href="#">MORE+</a>	Protective Window for #17-026		<a href="#">#17-695</a>	€870,00 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> 1
<a href="#">MORE+</a>	Protective Window for #16-771		<a href="#">#17-698</a>	€865,00 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> 1

## Related Products


Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

**Select Your Country/Region:**


## Resources

### Media Type


- Application Note
- Technical Tool
- Glossary
- Scientific Paper
- Video
- Published Article
- FAQ




**APPLICATION NOTE**  
Chromatically Corrected F-Theta Lenses for Ultrafast...



**APPLICATION NOTE**  
Anti-Reflection (AR) Coatings



**TECHNICAL TOOL**  
Gaussian Beams Calculator



**GLOSSARY**  
F-Theta Scanning Lens



**SCIENTIFIC PAPER**  
Development of a Robust Laser Damage Threshold...



**SCIENTIFIC PAPER**  
Development of US national laser damage standard: 20...

[View More](#)