

[See all 32 Products in Family](#)

1064nm, 6-9mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal πShaper_1064_Q-7.5

See More by [AdlOptica](#)



Focal Flat Top Beam Shaper



Stock #12-232 **1 In Stock**

⊖ 1 ⊕ €2.815⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€2.815,00 each
Qty 5-10	€2.535,00 each
Qty 11+	€2.395,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Model Number:
πShaper_1064_Q-7.5

Type:
Beam Shaper

#12-322

Compatible Adapter:

Physical & Mechanical Properties

29.00 Length (mm):

50 Weight (g):

20 Clear Aperture CA (mm):

42.00 Diameter (mm):

6 - 9 Input Beam Diameter, $1/e^2$ (mm):

Optical Properties

>99 Transmission (%):

1064 Design Wavelength DWL (nm):

1020 - 1100 Wavelength Range (nm):

TEM₀₀ Input Beam Mode:

<1.5 Typical Input Beam Mode Quality, M^2 :

±20 Input Beam Divergence (mrad):

Electrical

0.2 Maximum Input Power, CW (kW):

Threading & Mounting

M30 x 0.75 Inner Thread:

M30 x 0.75 Outer Thread:

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 250:

Product Details

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica πShaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal-πShaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal-πShapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

Technical Information

